

CB 750/7,5 BK


Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



CB cable ties for the fastening of cables and markers.

- They are particularly suitable for fastening CLI M, SFX, WKM and WKS cable markers
- IEC 62275: 2006-conformant
- Fracture-resistant polyamide PA 6.6 with flammability rating V2 to UL-94

General ordering data

Version	Cable ties, 7.5 x 750 mm, Polyamide 66, 540 N
Order No.	1720670000
Type	CB 750/7,5 BK
GTIN (EAN)	4008 190362355
Qty.	100 items

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (UR) E317499

Dimensions and weights

Depth	2 mm	Depth (inches)	0.0787 inch
Height	750 mm	Height (inches)	29.5275 inch
Width	7.5 mm	Width (inches)	0.2953 inch
Net weight	10.13 g		

Temperatures

Operating temperature range -40...85 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption

REACH SVHC No SVHC above 0.1 wt%

Installation materials

UV-resistant	No	For re-opening	No
UL 94 flammability rating	V-2	Operating temperature range, max.	85 °C
Operating temperature range, min.	-40 °C	Halogen	No
Cable diameter, max.	220 mm	Basic material	Polyamide 66
Tensile strength	540 N	Bundle diameter, max.	220 mm
Tensile strength (Pound-force)	121 lbf	Bundle diameter, min.	35 mm

Classifications

ETIM 8.0	EC000046	ETIM 9.0	EC000046
ETIM 10.0	EC000046	ECLASS 14.0	27-14-07-02
ECLASS 15.0	27-14-07-02		

Drawings

