

**CB 750/7,5 NC****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



CB cable ties for the fastening of cables and markers.

- They are particularly suitable for fastening CLI M, SFX, WKM and WKS cable markers
- IEC 62275: 2006-conformant
- Fracture-resistant polyamide PA 6.6 with flammability rating V2 to UL-94

**General ordering data**

Version	Cable ties, 7.5 x 750 mm, Polyamide 66, 540 N
Order No.	<a href="#">1720680000</a>
Type	CB 750/7,5 NC
GTIN (EAN)	4008 190362362
Qty.	1200 items

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate No. (UR)	E317499

Dimensions and weights

Depth	1.3 mm	Depth (inches)	0.0512 inch
Height	750 mm	Height (inches)	29.5275 inch
Width	7.5 mm	Width (inches)	0.2953 inch
Net weight	10 g		

Temperatures

Operating temperature range	-40...85 °C
-----------------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Installation materials

UV-resistant	No	For re-opening	No
UL 94 flammability rating	V-2	Operating temperature range, max.	85 °C
Operating temperature range, min.	-40 °C	Halogen	No
Cable diameter, max.	220 mm	Basic material	Polyamide 66
Tensile strength	540 N	Bundle diameter, max.	220 mm
Tensile strength (Pound-force)	121 lbf	Bundle diameter, min.	35 mm

Important note

Product information	Number of bags in box (pieces): 12 Number of items in bag (pieces): 100 One delivery unit corresponds to one box quantity, and only multiples of the delivery unit can be ordered.
---------------------	------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Classifications

ETIM 8.0	EC000046	ETIM 9.0	EC000046
ETIM 10.0	EC000046	ECLASS 14.0	27-14-07-02
ECLASS 15.0	27-14-07-02		

**Drawings**

