



CB cable ties for the fastening of cables and markers.

- They are particularly suitable for fastening CLI M, SFX, WKM and WKS cable markers
- IEC 62275: 2006-conformant
- Fracture-resistant polyamide PA 6.6 with flammability rating V2 to UL-94

### General ordering data

Version	Cable ties, 4,5 x 160 mm, Polyamide 66, 220 N
Order No.	<a href="#">1723540000</a>
Type	CB 160/4,5 NC
GTIN (EAN)	4008 190366247
Qty.	7000 items

## Technical data

### Approvals

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate No. (UR)	E317499

### Dimensions and weights

Depth	1.3 mm	Depth (inches)	0.0512 inch
Height	160 mm	Height (inches)	6.2992 inch
Width	4.5 mm	Width (inches)	0.1772 inch
Net weight	1.02 g		

### Temperatures

Operating temperature range	-40...85 °C
-----------------------------	-------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Installation materials

UV-resistant	No	For re-opening	No
UL 94 flammability rating	V-2	Operating temperature range, max.	85 °C
Operating temperature range, min.	-40 °C	Halogen	No
Cable diameter, max.	40 mm	Basic material	Polyamide 66
Tensile strength	220 N	Bundle diameter, max.	38 mm
Tensile strength (Pound-force)	49 lbf	Bundle diameter, min.	2.5 mm

### Important note

Product information	Number of bags in box (pieces): 70 Number of items in bag (pieces): 100 One delivery unit corresponds to one box quantity, and only multiples of the delivery unit can be ordered.
---------------------	--

### Classifications

ETIM 8.0	EC000046	ETIM 9.0	EC000046
ETIM 10.0	EC000046	ECLASS 14.0	27-14-07-02
ECLASS 15.0	27-14-07-02		

**Drawings**

