



CB cable ties for the fastening of cables and markers.

- They are particularly suitable for fastening CLI M, SFX, WKM and WKS cable markers
- IEC 62275: 2006-conformant
- Fracture-resistant polyamide PA 6.6 with flammability rating V2 to UL-94

General ordering data

Version	Cable ties, 4.8 x 178 mm, Polyamide 66, 220 N
Order No.	1723550000
Type	CB 178/4,8 NC
GTIN (EAN)	4008 190366254
Qty.	100 items

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (UR) E317499

Dimensions and weights

Depth	1.3 mm	Depth (inches)	0.0512 inch
Height	178 mm	Height (inches)	7.0079 inch
Width	4.8 mm	Width (inches)	0.189 inch
Net weight	1.15 g		

Temperatures

Operating temperature range -40...85 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption

REACH SVHC No SVHC above 0.1 wt%

Installation materials

UV-resistant	No	For re-opening	No
UL 94 flammability rating	V-2	Operating temperature range, max.	85 °C
Operating temperature range, min.	-40 °C	Halogen	No
Cable diameter, max.	45 mm	Basic material	Polyamide 66
Tensile strength	220 N	Bundle diameter, max.	45 mm
Tensile strength (Pound-force)	49 lbf	Bundle diameter, min.	2 mm

Classifications

ETIM 8.0	EC000046	ETIM 9.0	EC000046
ETIM 10.0	EC000046	ECLASS 14.0	27-14-07-02
ECLASS 15.0	27-14-07-02		

Drawings

