


BS 35II KLBUE HOLDER

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image

The comprehensive accessories of the Klippon® Connect portfolio are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms

General ordering data

Version	Clamping yoke, Set of fixings, Steel
Order No.	1723800000
Type	BS 35II KLBUE HOLDER
GTIN (EAN)	4008 1903 77038
Qty.	10 items

BS 35II KLBUE HOLDER

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	36.5 mm	Depth (inches)	1.437 inch
Height	35 mm	Height (inches)	1.378 inch
Diameter	3 mm	Net weight	38.5 g

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	Steel	Colour	silver
----------------	-------	--------	--------

System specifications

Version	Clamping yoke	Mounting rail	TS 35
---------	---------------	---------------	-------

Additional technical data

Type of fixing	when screwed in	Installation advice	Direct mounting
Explosion-tested version	Yes		

Dimensions

Diameter	3 mm	TS 35 offset	26.5 mm
----------	------	--------------	---------

General

Installation advice	Direct mounting	Mounting rail	TS 35
---------------------	-----------------	---------------	-------

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		