


**BS 35II/KLBUE 4-13.5**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**

With our wide range of KLBÜ shield connections, you can achieve flexible and self-adjusting shield contacting and ensure error-free plant operation.

**General ordering data**

Version	Clamping yoke, Set of fixings, Steel
Order No.	<a href="#">1723820000</a>
Type	BS 35II/KLBUE 4-13.5
GTIN (EAN)	4008190377014
Qty.	10 items

**BS 35II/KLBUE 4-13.5**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	36.5 mm	Depth (inches)	1.437 inch
Height	35 mm	Height (inches)	1.378 inch
Diameter	3 mm	Net weight	68.96 g

**Temperatures**

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Material data**

Basic material	Steel	Colour	silver
----------------	-------	--------	--------

**System specifications**

Version	Clamping yoke
---------	---------------

**Additional technical data**

Type of fixing	when screwed in	Explosion-tested version	Yes
----------------	-----------------	--------------------------	-----

**Conductors for clamping (rated connection)**

Cable diameter, max.	13.5 mm	Cable diameter, min.	4 mm
----------------------	---------	----------------------	------

**Dimensions**

Diameter	3 mm
----------	------

**Classifications**

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		