

FM 4.2/TS35**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image

The comprehensive accessories of the Klippon® Connect portfolio are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms

General ordering data

Version	Mounting foot on mounting rail, silver, Steel, bright finish, M 4, Width: 14 mm
Order No.	1724580000
Type	FM 4.2/TS35
GTIN (EAN)	4008 190377717
Qty.	40 items

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	7 mm	Depth (inches)	0.2756 inch
Height	50.2 mm	Height (inches)	1.9764 inch
Width	14 mm	Width (inches)	0.5512 inch
Net weight	4.5 g		

Temperatures

Ambient temperature	-5 °C...40 °C
---------------------	---------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	Steel, bright finish	Surface finish	nickel-plated
Colour	silver		

System specifications

Version	For the mounting rails	Mounting rail	TS 35
---------	------------------------	---------------	-------

Additional technical data

Type of fixing	Snap-on	Explosion-tested version	No
----------------	---------	--------------------------	----

Dimensions

Internal thread	M 4	Pitch in mm (P)	14.00 mm
Fixing dimension	4.2 mm		

General

Surface finish	nickel-plated	Mounting rail	TS 35
----------------	---------------	---------------	-------

Classifications

ETIM 8.0	EC002625	ETIM 9.0	EC002625
ETIM 10.0	EC002625	ECLASS 14.0	27-18-28-07
ECLASS 15.0	27-18-28-07		

Drawings

