

**GWDR M63-NP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

|            |  |
|------------|--|
| Version    | GWDR NP (flat gasket - neoprene), Sealing ring, M 63, Neoprene |
| Order No.  | <a href="#">1736290000</a>                                     |
| Type       | GWDR M63-NP  |
| GTIN (EAN) | 4008 190956080   |
| Qty.       | 10 items   |

## GWDR M63-NP

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Dimensions and weights

|            |       |                 |             |
|------------|-------|-----------------|-------------|
| Height     | 2 mm  | Height (inches) | 0.0787 inch |
| Net weight | 4.8 g |                 |             |

### Temperatures

|                       |                  |
|-----------------------|------------------|
| Operating temperature | -40 °C... 100 °C |
|-----------------------|------------------|

### Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

### General information

|                                   |          |                                   |          |
|-----------------------------------|----------|-----------------------------------|----------|
| Silicone                          | No       | Number of wires                   | 1        |
| O.D.                              | 77 mm    | Operating temperature range, max. | 100 °C   |
| Operating temperature range, min. | -40 °C   | Pitch of thread                   | 1.5 mm   |
| Halogen                           | Yes      | Thickness                         | 2.00 mm  |
| Cable gland                       | M 63     | Basic material                    | Neoprene |
| Diameter of sealing ring          | 77.00 mm | Sealing                           | Neoprene |
| External thread                   | M 63     | Internal thread                   | M 63     |
| Inside diameter D2                | 63.00 mm |                                   |          |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001181    | ETIM 9.0    | EC001181    |
| ETIM 10.0   | EC001181    | ECLASS 14.0 | 27-43-03-19 |
| ECLASS 15.0 | 27-43-03-19 |             |             |

**Drawings**

