

**GWDR M63-NP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Version	GWDR NP (flat gasket - neoprene), Sealing ring, M 63, Neoprene
Order No.	<a href="#">1736290000</a>
Type	GWDR M63-NP
GTIN (EAN)	4008 190956080
Qty.	10 items

**GWDR M63-NP**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Height	2 mm	Height (inches)	0.0787 inch
Net weight	4.8 g		

**Temperatures**

Operating temperature -40 °C...100 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General information**

Silicone	No	Number of wires	1
O.D.	77 mm	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Pitch of thread	1.5 mm
Halogen	Yes	Thickness	2.00 mm
Cable gland	M 63	Basic material	Neoprene
Diameter of sealing ring	77.00 mm	Sealing	Neoprene
External thread	M 63	Internal thread	M 63
Inside diameter D2	63.00 mm		

**Classifications**

ETIM 8.0	EC001181	ETIM 9.0	EC001181
ETIM 10.0	EC001181	ECLASS 14.0	27-43-03-19
ECLASS 15.0	27-43-03-19		

**GWDR M63-NP**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)

