

SZS M25**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	SZS (serrated washer), Retaining toothed washers, M 25, Stainless steel 1.4404 (316L)
Order No.	1736320000
Type	SZS M25
GTIN (EAN)	4008 19096352 1
Qty.	10 items
Delivery status	Discontinued
Available until	2024-08-31T00:00:00+02:00

SZS M25

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Height	4.5 mm	Height (inches)	0.1772 inch
Net weight	6.88 g		

Temperatures

Operating temperature

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General information

O.D.	37.4 mm	Pitch of thread	1.5 mm
Halogen	halogen-free	Thickness	1.90 mm
Cable gland	metric	Basic material	Stainless steel 1.4404 (316L)
External thread	M 25	Internal thread	M 25
Inside diameter D2	25.30 mm		

Classifications

ETIM 8.0	EC002345	ETIM 9.0	EC002345
ETIM 10.0	EC002345	ECLASS 14.0	27-14-08-07
ECLASS 15.0	27-14-08-07		

SZS M25

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

