

EA-RING MS/M 25

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	EA (earthing rings), Earthing ring, Miscellaneous, M 25, Brass, nickel-plated
Order No.	1736500000
Type	EA-RING MS/M 25
GTIN (EAN)	4008 190963606
Qty.	20 items

EA-RING MS/M 25

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Height	61.5 mm	Height (inches)	2.4213 inch
Length	61.5 mm	Length (inches)	2.4213 inch
Net weight	8.1 g		

Temperatures

Operating temperature

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	2bd73422-c6ea-4a92-b8e7-00964d1156f3

Certificate numbers cable gland

Identification Ex e II, II 2 GD, EEx d II

General information

O.D.	34 mm	Thickness	1.50 mm
Cable gland	M 25	Basic material	Brass, nickel-plated
External thread	M 25	Inside diameter D2	10.50 mm
Gap, internal dimension B	36.00 mm	Width, outer dimension C	17.00 mm

Classifications

ETIM 8.0	EC002317	ETIM 9.0	EC002317
ETIM 10.0	EC002317	ECLASS 14.0	27-14-08-07
ECLASS 15.0	27-14-08-07		

EA-RING MS/M 25

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

