

KSP L30**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	KSP (Klippon shroud), Protective cap, PVC
Order No.	1736580000
Type	KSP L30
GTIN (EAN)	4008190956233
Qty.	10 items
Delivery status	Discontinued
Available until	2023-07-30T00:00:00+02:00

KSP L30

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Height	120 mm	Height (inches)	4.7244 inch
Length	130 mm	Length (inches)	5.1181 inch
Wall thickness, min.	2 mm	Wall thickness, max.	2 mm
Net weight	26 g		

Temperatures

Operating temperature	-25 °C...70 °C
-----------------------	----------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General information

Silicone	No	O.D.	34 mm
Operating temperature range, max.	70 °C	Operating temperature range, min.	-25 °C
Halogen	No	Thickness	2.00 mm
Basic material	PVC	Inside diameter D2	30.00 mm
Gap, internal dimension B	75.00 mm	Hardness (Shore A)	65

Classifications

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-07
ECLASS 15.0	27-14-08-07		

Drawings

