

KSP L55**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	KSP (Klippon shroud), Protective cap, PVC
Order No.	1736610000
Type	KSP L55
GTIN (EAN)	4008190956271
Qty.	10 items
Delivery status	Discontinued
Available until	2023-07-30T00:00:00+02:00

KSP L55

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Height	160 mm	Height (inches)	6.2992 inch
Length	150 mm	Length (inches)	5.9055 inch
Wall thickness, min.	2 mm	Wall thickness, max.	2 mm
Net weight	58.6 g		

Temperatures

Operating temperature	-25 °C...70 °C
-----------------------	----------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General information

Silicone	No	O.D.	59 mm
Operating temperature range, max.	70 °C	Operating temperature range, min.	-25 °C
Halogen	No	Thickness	2.00 mm
Basic material	PVC	Inside diameter D2	55.00 mm
Gap, internal dimension B	85.00 mm	Hardness (Shore A)	65

Classifications

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-07
ECLASS 15.0	27-14-08-07		

Drawings

