

SKMU M32 K SW**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	SKMU PA (plastic locknut), Locknut, M 32, 7 mm, Polyamid 6 (PA6 - GF30)
Order No.	1736950000
Type	SKMU M32 K SW
GTIN (EAN)	4008 190956424
Qty.	100 items

SKMU M32 K SW

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Height	7 mm	Height (inches)	0.2756 inch
Net weight	5.61 g		

Temperatures

Operating temperature -40 °C...100 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General information

Silicone	No	O.D.	47.36 mm
UL 94 flammability rating	HB	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Pitch of thread	1.5 mm
Halogen	No	AF size 1	41 mm
Thickness	7.00 mm	Cable gland	M 32
Basic material	Polyamid 6 (PA6 - GF30)	External thread	M 32
Internal thread	M 32	Length of thread	7 mm

Classifications

ETIM 8.0	EC000940	ETIM 9.0	EC000940
ETIM 10.0	EC000940	ECLASS 14.0	27-14-08-07
ECLASS 15.0	27-14-08-07		

SKMU M32 K SW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

