

**SKMU M32 MS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

|            |  |
|------------|--|
| Version    | SKMU MS (brass locknut), Locknut, M 32, 4 mm, Brass, nickel-plated |
| Order No.  | <a href="#">1737020000</a>   |
| Type       | SKMU M32 MS  |
| GTIN (EAN) | 4008 190956493   |
| Qty.       | 100 items  |

**SKMU M32 MS**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Height     | 4 mm   | Height (inches) | 0.1575 inch |
| Net weight | 2.12 g |                 |             |

**Temperatures**

Operating temperature

**Environmental Product Compliance**

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status               | Compliant with exemption             |
| RoHS Exemption (if applicable/known) | 6c                                   |
| REACH SVHC                           | Lead 7439-92-1                       |
| SCIP                                 | f350dea6-3de1-42c5-a935-c4eb3e9d5e3c |

**General information**

|                 |                      |                  |        |
|-----------------|----------------------|------------------|--------|
| O.D.            | 41.58 mm             | Pitch of thread  | 1.5 mm |
| Halogen         | No                   | AF size 1        | 36 mm  |
| Thickness       | 4.00 mm              | Cable gland      | M 32   |
| Basic material  | Brass, nickel-plated | External thread  | M 32   |
| Internal thread | M 32                 | Length of thread | 4 mm   |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000940    | ETIM 9.0    | EC000940    |
| ETIM 10.0   | EC000940    | ECLASS 14.0 | 27-14-08-05 |
| ECLASS 15.0 | 27-14-08-05 |             |             |

Drawings

