Data sheet

ADAP EX M40-1/2NPT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration



ADAP series adaptors provide flexibility and versatility infilling unused entries in Ex equipment while maintaining Flameproof Ex d and Increased Safety Ex e explosion protection and IP66/67/68 ingress rate.

General ordering data

Version	ADAP (adaptor, extensions and reductions), Adapter, straight, M 40 ,1/2" NPT, IP54, Brass, nickel-plated
Order No.	1738450000
Type	ADAP EX M40-1/2NPT
GTIN (EAN)	4008190958237
Qty.	1 items
Delivery status	Discontinued
Available until	2023-07-30T00:00:00+02:00

ADAP EX M40-1/2NPT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform

Dimensions and weights

Net weight	156 g

Temperatures

Operating temperature	-40 °C...100 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	69c399a3-d29f-4fa4-b22e-340c0db02257

Certificate numbers cable gland

Identification	II 2 GD, Ex d IIC, Ex e II, Ex tD	Certificate no. cable gland (ATEX)	SIRA 10ATEX1225X
Certificate no. cable gland (IECEx)	IECEx SIR 07.0010X	Approval conditions	ATEX, IECEX

General information

Protection degree with GWDR	IP54	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Halogen	halogen-free
AF size 1	47 mm	Protection degree	IP54
Cable gland	NPT	Basic material	Brass, nickel-plated
External thread	M 40	Internal thread	1/2" NPT
Length of thread	16 mm	Note: protection class	Please follow the operating instructions to attain higher IP protection.

Classifications

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-06
ECLASS 15.0	27-14-08-06		

ADAP EX M40-1/2NPT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Brass lock nuts, nickel-plated



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SKMU M40 MS	Version
Order No.	1737030000	SKMU MS (brass locknut), Locknut, M 40, 5 mm, Brass, nickel-plated
GTIN (EAN)	4008190956509	
Qty.	50 ST	

Nylon flat washer - GWDR



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	GWDR M40-W	Version
Order No.	1185640000	in closed state, M 40, Nylon 6
GTIN (EAN)	4050118078336	
Qty.	50 ST	