

SCHS4 K

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



General ordering data

Version	Device markers, Accessories x 10 mm, PVC, Colour: grey, Self-adhesive
Order No.	1753460000
Type	SCHS4 K
GTIN (EAN)	4032248014323
Qty.	50 items

SCHS4 K

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	6 mm	Depth (inches)	0.2362 inch
Height	1000 mm	Height (inches)	39.37 inch
Width	10 mm	Width (inches)	0.3937 inch
Net weight	19 g		

Temperatures

Operating temperature range -20...80 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

Adhesive	Double-sided adhesive tape		
Material colour according to resistance code	8		
Version	Self-adhesive		
Width	10 mm		
UL 94 flammability rating	V-0		
Operating temperature range, max.	80 °C		
Operating temperature range, min.	-20 °C		
Colour	grey		
Halogen	No		
Basic material	PVC		
Number of markers per packaging unit	Form of supply	MultiCard	
Number of markers per combination	1 MultiCard = Accessories		
Operating temperature range	-20...80 °C		
Application/manufacturer	Self-adhesive		

Device markers

Halogen No

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

