

BS 35/WSH 2**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

The comprehensive accessories of the Klippon® Connect portfolio are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms

General ordering data

Version	Accessories, Set of fixings, Steel
Order No.	1760720000
Type	BS 35/WSH 2
GTIN (EAN)	4008 1900687 14
Qty.	10 items

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	37 mm	Depth (inches)	1.4567 inch
Height	52 mm	Height (inches)	2.0472 inch
Width	13 mm	Width (inches)	0.5118 inch
Diameter	3 mm	Net weight	27.1 g

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	Steel	Colour	grey
----------------	-------	--------	------

System specifications

Version	Mounting foot	Mounting rail	TS 35
---------	---------------	---------------	-------

Additional technical data

Type of fixing	when screwed in	Installation advice	Direct mounting
Explosion-tested version	No	Locking	for screw fixing

Dimensions

Diameter	3 mm	TS 35 offset	26 mm
----------	------	--------------	-------

General

Installation advice	Direct mounting	Mounting rail	TS 35
---------------------	-----------------	---------------	-------

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		