

**SCHT 5 V0****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



The SchT 5 S group tag carriers are clipped directly onto the TS 32 mounting rail (G-rail) or the TS 35 mounting rail (top-hat rail). It is therefore possible to label the terminal strip irrespective of the terminal and the type of terminal. SchT 5 and SchT 5 S are fitted with ESO 5, STR 5 protective strips.

The SchT 7 is a hinged group tag carrier for inlay tags which enables easy access to the clamping screw.

The SchT 7 is fitted with ESO 7, STR 7 protective strips or DEK 5.

Inlay tags and protective strips can be found under "Accessories".

**General ordering data**

Version	SCHT, Terminal marker, 44.5 x 19.5 mm, Pitch in mm (P): 5.00 beige
Order No.	<a href="#">1762360000</a>
Type	SCHT 5 V0
GTIN (EAN)	4032248043835
Qty.	20 items

**SCHT 5 V0**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Height	44.5 mm	Height (inches)	1.752 inch
Width	19.5 mm	Width (inches)	0.7677 inch
Net weight	8.15 g		

**Temperatures**

Operating temperature range -40...120 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General data**

Orientation of print	horizontal and vertical	
Type of printing	neutral	
Width	19.5 mm	
UL 94 flammability rating	V-0	
Operating temperature range, max.	120 °C	
Operating temperature range, min.	-40 °C	
Colour	beige	
Halogen	No	
Basic material	Polyamide 66	
Printed characters	without	
Number of markers per packaging unit	Form of supply	Component part
Number of markers per combination	1 Component part = Terminal marker	
Operating temperature range	-40...120 °C	

**Connector markers**

Pitch in mm (P) 5.00 mm

**Classifications**

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-14-11-92
ECLASS 15.0	27-14-11-92		