

THM MT30X 101/74 SI

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The THM labels offer brilliant printing quality thanks to the thermal transfer technology. Different materials and the user-friendly printing system under Windows optimise every marking effort.

- High-quality polyester labels in various colours or inexpensive paper labels are available
- Labels are automatically positioned in the printer for perfectly centred prints on each label.

General ordering data

| | |
|------------|--|
| Version | THM, Device markers, 74 x 101 mm, silver |
| Order No. | 1762960001 |
| Type | THM MT30X 101/74 SI |
| GTIN (EAN) | 4032248220410 |
| Qty. | 1 items |

THM MT30X 101/74 SI

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 0.08 mm | Depth (inches) | 0.0031 inch |
| Height | 74 mm | Height (inches) | 2.9134 inch |
| Width | 101 mm | Width (inches) | 3.9764 inch |
| Net weight | 640 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -40...150 °C |
|-----------------------------|--------------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

General data

| | | |
|--------------------------------------|--|------------|
| Adhesive | Acrylate adhesive | |
| Printing method | Thermal transfer | |
| Version | Self-adhesive, halogen-free | |
| Width | 101 mm | |
| UL 94 flammability rating | V-0 | |
| Operating temperature range, max. | 150 °C | |
| Operating temperature range, min. | -40 °C | |
| Colour | silver | |
| Halogen | No | |
| Basic material | Polyester | |
| Printed characters | without | |
| Number of markers per packaging unit | Form of supply | Label reel |
| Approval acc. to UL 969 | Yes | |
| compatible printer | THM MULTIMARK , THM MULTIMARK PLUS | |
| Number of markers per combination | 1 Label reel = Device markers | |
| Operating temperature range | -40...150 °C | |
| Number per roll | 500 | |

Device markers

| | |
|---------|----|
| Halogen | No |
|---------|----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001288 | ETIM 9.0 | EC001288 |
| ETIM 10.0 | EC001288 | ECLASS 14.0 | 27-28-11-04 |
| ECLASS 15.0 | 27-28-11-04 | | |

Drawings

