



CLI M identification markers are slid onto CLI MH carrier strips and secured by means of cable ties. The system is particularly suitable for large conductor and cable cross-sections. Advantages:

- Combination marker for cable and pipe markers
- One size for all diameters above 16 mm<sup>2</sup>
- Unrestricted combination options
- Closed, permanently attached markers
- Very good legibility

### General ordering data

Version	CableLine, Conductor and cable markers, 10 - 317 mm, 33 x 11.3 mm, Transparent
Order No.	<a href="#">1763280000</a>
Type	CLI TM 20-33
GTIN (EAN)	4032248050246
Qty.	100 items

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	5 mm	Depth (inches)	0.1968 inch
Height	33 mm	Height (inches)	1.2992 inch
Width	11.3 mm	Width (inches)	0.4449 inch
Net weight	0.62 g		

### Temperatures

Operating temperature range	-30...60 °C
-----------------------------	-------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### General data

Type of printing	neutral	
Width	11.3 mm	
UL 94 flammability rating	V-0	
Operating temperature range, max.	60 °C	
Operating temperature range, min.	-30 °C	
Colour	Transparent	
Halogen	Yes	
Basic material	PVC	
Number of markers per packaging unit	Form of supply	Component part
Recommended industries	Process, Machinery	
Number of markers per combination	1 Component part = Conductor and cable markers	
Operating temperature range	-30...60 °C	

### Conductor and cable markers


Halogen	Yes	Conductor cross-section, max.	500 mm <sup>2</sup>
Conductor cross-section, min.	16 mm <sup>2</sup>	Conductor O.D., max.	317 mm
Conductor O.D., min.	10 mm	Conductor O.D.	10 - 317 mm
Cross-section for connected wire	16 - 500 mm <sup>2</sup>		

### Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

## Accessories

### Blank



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### General ordering data

Type	ESG 9/17 K MC NE WS	Version	
Order No.	<a href="#">1674760000</a>		ESG, Device markers x 17 mm, PA 66, Colour: white, Self-adhesive
GTIN (EAN)	4008190447649		
Qty.	200 ST		