

ESG 8/17 SCHS MC SDR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Version	ESG, Device markers x 17 mm, PA 66, Colour: To customer specification, pluggable
Order No.	1766640000
Type	ESG 8/17 SCHS MC SDR
GTIN (EAN)	4032248065530
Qty.	40 items

ESG 8/17 SCHS MC SDR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	0.8 mm	Depth (inches)	0.0315 inch
Height	8 mm	Height (inches)	0.315 inch
Width	17 mm	Width (inches)	0.6693 inch
Net weight	0.38 g		

Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Product Carbon Footprint	Cradle to gate	0.005 kg CO2 eq.	

General data

Printing method	MC Laser		
Version	pluggable		
Width	17 mm		
UL 94 flammability rating	V-2		
Operating temperature range, max.	100 °C		
Operating temperature range, min.	-40 °C		
Colour	To customer specification		
Halogen	No		
Basic material	PA 66		
Colour of printing	black		
Printed characters	Requires M-Print PRO File		
Number of markers per packaging unit	Form of supply	MultiCard	
compatible printer	PRINTJET CONNECT , MCP BASIC 2 , MCP PLUS 2		
Number of markers per combination	1 MultiCard = Device markers		
Operating temperature range	-40... 100 °C		
Application/manufacturer	Tag rail SchS2		

Device markers

Halogen	No
---------	----

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

Drawings



ESG 8/17 SCHS MC SDR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories**Accessories****General ordering data**

Type	SCHS2 K	Version
Order No.	1720600000	Device markers, Accessories x 8 mm, PVC, Colour: black, Self-adhesive
GTIN (EAN)	4008190362270	
Qty.	50 ST	
Type	SCHS2	Version
Order No.	0337400000	Device markers, Accessories, 1000 x 8 mm, PVC, Colour: black, Marker holder
GTIN (EAN)	4032248396047	
Qty.	50 ST	