


**ESG 7/20 SIRIUS MC SDR**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com



Similar to illustration

ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

Version	ESG, Device markers x 20 mm, PA 66, Colour: To customer specification, pluggable
Order No.	<a href="#">1766650000</a>
Type	ESG 7/20 SIRIUS MC SDR
GTIN (EAN)	4032248065547
Qty.	40 items

## ESG 7/20 SIRIUS MC SDR

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	0.8 mm	Depth (inches)	0.0315 inch
Height	7 mm	Height (inches)	0.2756 inch
Width	20 mm	Width (inches)	0.7874 inch
Net weight	0.28 g		

## Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption	
REACH SVHC	No SVHC above 0.1 wt%	
Product Carbon Footprint	Cradle to gate	0.005 kg CO2 eq.

## General data

Number per sheet	40	
Printing method	MC Laser	
Version	pluggable	
Width	20 mm	
UL 94 flammability rating	V-2	
Operating temperature range, max.	100 °C	
Operating temperature range, min.	-40 °C	
Colour	To customer specification	
Halogen	No	
Basic material	PA 66	
Colour of printing	black	
Printed characters	Requires M-Print PRO File	
Number of markers per packaging unit	Form of supply	MultiCard
compatible printer	<a href="#">PRINTJET CONNECT, MCP BASIC 2, MCP PLUS 2</a>	
Number of markers per combination	1 MultiCard = Device markers	
Operating temperature range	-40...100 °C	
Application/manufacturer	Siemens Sirius 3R	

## Device markers

Halogen	No
---------	----

## Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		



## ESG 7/20 SIRIUS MC SDR

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

## Accessories

www.weidmueller.com

### Accessories



### General ordering data

Type	SCHS3 K	Version	
Order No.	<a href="#">1753480000</a>	Device markers, Accessories x 10 mm, PVC, Colour: black, Self-adhesive	
GTIN (EAN)	4032248014347		
Qty.	50 ST		
Type	SCHS4 K	Version	
Order No.	<a href="#">1753460000</a>	Device markers, Accessories x 10 mm, PVC, Colour: grey, Self-adhesive	
GTIN (EAN)	4032248014323		
Qty.	50 ST		