

**KSBR/3 ZTL6****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

**General ordering data**

Version	Accessories, Cross-connector, 10 A
Order No.	<a href="#">1771830000</a>
Type	KSBR/3 ZTL6
GTIN (EAN)	403224812665 1
Qty.	20 items

## KSBR/3 ZTL6

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS Conform

## Dimensions and weights

Height	32.9 mm	Height (inches)	1.2953 inch
Width	23.2 mm	Width (inches)	0.9134 inch
Net weight	6.12 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-50 °C...75 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Material data

Basic material	Wemid	Colour	yellow
UL 94 flammability rating	V-0		

## System specifications

Version For the terminals

## Additional technical data

Type of fixing	Plugged	Installation advice	Direct mounting
Explosion-tested version	No		

## Dimensions

Pitch in mm (P) 8.00 mm

## General

Number of poles	3	Installation advice	Direct mounting
-----------------	---	---------------------	-----------------

## Rating data

Rated voltage	400 V	Nominal current	10 A
---------------	-------	-----------------	------

## Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		