

## VG M20 - MS 68

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Similar to illustration



In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

### General ordering data

Version	VG MS (standard brass cable gland), Cable glands, straight, M 20, 8 mm, OD min. 6 - OD max. 12 mm, IP54, IP66, IP67, IP68 - 5 bar (30 min.), IP69K, Brass, nickel-plated
Order No.	<a href="#">1772220000</a>
Type	VG M20 - MS 68
GTIN (EAN)	4032248129874
Qty.	50 items

## VG M20 - MS 68

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

## Dimensions and weights

Height	29.5 mm	Height (inches)	1.1614 inch
Length	34.5 mm	Length (inches)	1.3583 inch
Net weight	28.2 g		

## Temperatures

Operating temperature -40 °C...100 °C

## Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	b5ff1f66-ddba-4739-9fc0-0521ddb52139

## Certificate numbers cable gland

Certificate no. cable gland (GERMLLOYD)	E-14047	Certificate no. cable gland (UL)	E-199260
Certificate no. cable gland (cULus)	E-199260	Approval conditions	DNV, UL, cULus

## General information

Outer cable diameter, max.	12 mm	Outer cable diameter, min.	6 mm
O-Ring	NBR	Protection degree with GWDR	IP54, IP66, IP67, IP68 - 5 bar (30 min.), IP69K
Tightening torque	5.5 Nm	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Pitch of thread	1.5 mm
Halogen	Yes	AF size 1	22 mm
AF size 2	22 mm	AF size	22 mm
Protection degree	IP54, IP66, IP67, IP68 - 5 bar (30 min.), IP69K	Cable gland	metric, M 20
Basic material	Brass, nickel-plated	Seal insert	CR
Sealing	NBR	External thread	M 20
Length of thread	8 mm	Torque for cap nut, max.	8.50 Nm
Protection class (UL)	Type 4X	Torque for connecting adapter, max.	6.00 Nm
Torque for connecting adapter, min.	5.00 Nm	Torque for cap nut, min.	7.50 Nm
Clamp insert	Polyamide		

## Classifications

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-01
ECLASS 15.0	27-14-08-01		

## VG M20 - MS 68

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### Brass lock nuts, nickel-plated



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

#### General ordering data

Type	SKMU M20 MS	Version	
Order No.	<a href="#">1737000000</a>	SKMU MS (brass locknut), Locknut, M 20, 3 mm, Brass, nickel-plated	
GTIN (EAN)	4008190956479		
Qty.	100 ST		

### Brass lock nuts, natural finish



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

#### General ordering data

Type	SKMU M20 MS SC	Version	
Order No.	<a href="#">0930640002</a>	SKMU MS (brass locknut), Locknut, M 20, 4 mm, Brass	
GTIN (EAN)	4032248849826		
Qty.	50 ST		

### Neoprene flat gasket - GWDR NP



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

#### General ordering data

Type	GWDR M20-NP	Version	
Order No.	<a href="#">1736240000</a>	GWDR NP (flat gasket - neoprene), Sealing ring, M 20, Neoprene	
GTIN (EAN)	4008190956035		
Qty.	50 ST		

## VG M20 - MS 68

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### Polyethylene flat gasket - GWDR PO



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

#### General ordering data

Type	GWDR M20-PO	Version	
Order No.	<a href="#">1777940000</a>	GWDR PO (flat gasket - polyethylene), Sealing ring, M 20,	
GTIN (EAN)	4032248158201	Polyethylene	
Qty.	100 ST		

### Vulcanised fibre gasket - KSWF



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

#### General ordering data

Type	KSWF M20	Version	
Order No.	<a href="#">0899750000</a>	KSWF (flat gasket - vulcanised fibre), Sealing ring, M 20, Vulcanized	
GTIN (EAN)	4032248850174	fibre	
Qty.	25 ST		

### Nylon flat gasket - KSWN



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

#### General ordering data

Type	KSWN M20	Version	
Order No.	<a href="#">0930730002</a>	KSWN (flat gasket - nylon), Sealing ring, M 20, Nylon 6	
GTIN (EAN)	4032248849802		
Qty.	25 ST		