


**AP 100 GR 7032****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The RS 100 Profi offers you a flexible solution for your mounting needs, as both DIN rail mounting and wall mounting are possible. This versatility facilitates integration into different environments and applications. The housing can be used for the Eurocard PCB standard. The profile can be cut to size so that you can adapt it precisely to your specific requirements. For particularly heavy components, additional locking feet can be used to improve stability and thus increase the safety of your installation.

Another practical feature is the option of using a cover profile to protect large components.

**General ordering data**

Version	SAK Series, End plate, 27.2 mm, grey, Direct mounting
Order No.	<a href="#">1773410000</a>
Type	AP 100 GR 7032
GTIN (EAN)	4032248141111
Qty.	20 items

**Technical data**

**Approvals**

ROHS	Conform
------	---------

**Dimensions and weights**

Depth	23.8 mm	Depth (inches)	0.937 inch
Height	104.8 mm	Height (inches)	4.126 inch
Width	27.2 mm	Width (inches)	1.0709 inch
Net weight	7.15 g		

**Temperatures**

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Material data**

UL 94 flammability rating	V-0	Basic material	PA 66
---------------------------	-----	----------------	-------

**General data**

Colour	grey	Protection degree	IP20
Colour chart (similar)	RAL 7035		

**Classifications**

ETIM 8.0	EC001031	ETIM 9.0	EC002779
ETIM 10.0	EC002779	ECLASS 14.0	27-19-06-02
ECLASS 15.0	27-19-06-02		