

**VP M16 K54****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Version	VPK (blanking plug in plastic), Blanking plug, in closed state, M 16, 7 mm, IP65, Polyamid 6 (PA6 - GF30)
Order No.	<a href="#">1776920000</a>
Type	VP M16 K54
GTIN (EAN)	4032248156368
Qty.	100 items

## VP M16 K54

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Height	4.5 mm	Height (inches)	0.1772 inch
Length	5.5 mm	Length (inches)	0.2165 inch
Diameter	16 mm	Wall thickness, min.	0.5 mm
Wall thickness, max.	6 mm	Net weight	1.6 g

## Temperatures

Operating temperature	-40 °C...100 °C
-----------------------	-----------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## General information

Head diameter	20.00 mm	Protection degree with GWDR	IP65
UL 94 flammability rating	V-2	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Pitch of thread	1.5 mm
Halogen	No	Protection degree	IP54
Cable gland	metric	Basic material	Polyamid 6 (PA6 - GF30)
Diameter of sealing ring	16.00 mm	External thread	M 16
Length of thread	7 mm		

## Classifications

ETIM 8.0	EC000451	ETIM 9.0	EC000451
ETIM 10.0	EC000451	ECLASS 14.0	27-14-08-05
ECLASS 15.0	27-14-08-05		

Drawings

