

VP M12 K54**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	VPK (blanking plug in plastic), Blanking plug, in closed state, M 12, 6 mm, IP65, Polyamid 6 (PA6 - GF30)
Order No.	1776930000
Type	VP M12 K54
GTIN (EAN)	4032248156375
Qty.	100 items

VP M12 K54

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Height	3 mm	Height (inches)	0.1181 inch
Length	5.5 mm	Length (inches)	0.2165 inch
Diameter	12 mm	Wall thickness, min.	0.5 mm
Wall thickness, max.	5 mm	Net weight	0.9 g

Temperatures

Operating temperature	-40 °C...100 °C
-----------------------	-----------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General information

Head diameter	15.00 mm	Protection degree with GWDR	IP65
UL 94 flammability rating	V-2	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Pitch of thread	1.5 mm
Halogen	No	Protection degree	IP54
Cable gland	metric	Basic material	Polyamid 6 (PA6 - GF30)
Diameter of sealing ring	12.00 mm	External thread	M 12
Length of thread	6 mm		

Classifications

ETIM 8.0	EC000451	ETIM 9.0	EC000451
ETIM 10.0	EC000451	ECLASS 14.0	27-14-08-05
ECLASS 15.0	27-14-08-05		

Drawings

