

VP M40 K54**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	VPK (blanking plug in plastic), Blanking plug, in closed state, M 40, 13 mm, IP65, Polyamid 6 (PA6 - GF30)
Order No.	1776950000
Type	VP M40 K54
GTIN (EAN)	4032248156399
Qty.	25 items

VP M40 K54

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Height	5 mm	Height (inches)	0.1968 inch
Length	7 mm	Length (inches)	0.2756 inch
Diameter	40 mm	Wall thickness, min.	0.5 mm
Wall thickness, max.	12 mm	Net weight	10.16 g

Temperatures

Operating temperature	-40 °C...100 °C
-----------------------	-----------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General information

Head diameter	46.00 mm	Protection degree with GWDR	IP65
UL 94 flammability rating	V-2	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Pitch of thread	1.5 mm
Halogen	No	Protection degree	IP54
Cable gland	metric	Basic material	Polyamid 6 (PA6 - GF30)
Diameter of sealing ring	40.00 mm	External thread	M 40
Length of thread	13 mm		

Classifications


ETIM 8.0	EC000451	ETIM 9.0	EC000451
ETIM 10.0	EC000451	ECLASS 14.0	27-14-08-05
ECLASS 15.0	27-14-08-05		

VP M40 K54

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com



VP M40 K54

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Plastic lock nuts, grey



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SKMU M40 - K GR	Version	
Order No.	1772490000	SKMU PA (plastic locknut), Locknut, M 40, 7 mm, Polyamid 6 (PA6 -	
GTIN (EAN)	4032248130238	GF30)	
Qty.	50 ST		

Neoprene flat gasket - GWDR NP



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	GWDR M40-NP	Version	
Order No.	1736270000	GWDR NP (flat gasket - neoprene), Sealing ring, M 40, Neoprene	
GTIN (EAN)	4008190956066		
Qty.	20 ST		

Polyethylene flat gasket - GWDR PO



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	GWDR M40-PO	Version	
Order No.	1777970000	GWDR PO (flat gasket - polyethylene), Sealing ring, M 40,	
GTIN (EAN)	4032248158232	Polyethylene	
Qty.	50 ST		