

SKMU EMV M16

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	SKMU MS EMV (brass locknut - EMC), Locknut, M 16, 3.6 mm, Brass, nickel-plated
Order No.	1777620000
Type	SKMU EMV M16
GTIN (EAN)	4032248157891
Qty.	100 items

SKMU EMV M16

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Height	4.7 mm	Height (inches)	0.185 inch
Net weight	1.85 g		

Temperatures

Operating temperature

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	f350dea6-3de1-42c5-a935-c4eb3e9d5e3c

General information

O.D.	20.79 mm	Pitch of thread	1.5 mm
Halogen	No	AF size 1	19 mm
Cable gland	M 16	Basic material	Brass, nickel-plated
External thread	M 16	Internal thread	M 16
Length of thread	3.6 mm		

Classifications

ETIM 8.0	EC000940	ETIM 9.0	EC000940
ETIM 10.0	EC000940	ECLASS 14.0	27-14-08-05
ECLASS 15.0	27-14-08-05		

Drawings

