

SKMU EMV M20

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

| | |
|------------|--|
| Version | SKMU MS EMV (brass locknut - EMC), Locknut, M 20, 3.6 mm, Brass, nickel-plated |
| Order No. | 1777630000 |
| Type | SKMU EMV M20 |
| GTIN (EAN) | 4032248157907 |
| Qty. | 100 items |

SKMU EMV M20

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

| | | | |
|------------|--------|-----------------|------------|
| Height | 4.7 mm | Height (inches) | 0.185 inch |
| Net weight | 5.8 g | | |

Temperatures

Operating temperature

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | f350dea6-3de1-42c5-a935-c4eb3e9d5e3c |

General information

| | | | |
|------------------|----------|-----------------|----------------------|
| O.D. | 26.56 mm | Pitch of thread | 1.5 mm |
| Halogen | No | AF size 1 | 24 mm |
| Cable gland | M 20 | Basic material | Brass, nickel-plated |
| External thread | M 20 | Internal thread | M 20 |
| Length of thread | 3.6 mm | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000940 | ETIM 9.0 | EC000940 |
| ETIM 10.0 | EC000940 | ECLASS 14.0 | 27-14-08-05 |
| ECLASS 15.0 | 27-14-08-05 | | |

SKMU EMV M20

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

