

## SKMU EMV M25

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Similar to illustration



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

### General ordering data

Version	SKMU MS EMV (brass locknut - EMC), Locknut, M 25, 3.6 mm, Brass, nickel-plated
Order No.	<a href="#">1777640000</a>
Type	SKMU EMV M25
GTIN (EAN)	4032248157914
Qty.	50 items

**SKMU EMV M25**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Height	5.2 mm	Height (inches)	0.2047 inch
Net weight	10.7 g		

**Temperatures**

Operating temperature

**Environmental Product Compliance**

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	f350dea6-3de1-42c5-a935-c4eb3e9d5e3c

**General information**

O.D.	30 mm	Pitch of thread	1.5 mm
Halogen	No	AF size 1	30 mm
Cable gland	M 25	Basic material	Brass, nickel-plated
External thread	M 25	Internal thread	M 25
Length of thread	3.6 mm		

**Classifications**

ETIM 8.0	EC000940	ETIM 9.0	EC000940
ETIM 10.0	EC000940	ECLASS 14.0	27-14-08-05
ECLASS 15.0	27-14-08-05		

**Drawings**

