

**GWDR M32-PO****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

|            |                                                                        |
|------------|------------------------------------------------------------------------|
| Version    | GWDR PO (flat gasket - polyethylene), Sealing ring, M 32, Polyethylene |
| Order No.  | <a href="#">1777960000</a>                                             |
| Type       | GWDR M32-PO                                                            |
| GTIN (EAN) | 4032248158225                                                          |
| Qty.       | 50 items                                                               |

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Height     | 2 mm   | Height (inches) | 0.0787 inch |
| Net weight | 0.35 g |                 |             |

**Temperatures**

Operating temperature -30 °C...90 °C

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

**General information**

|                                   |              |                                   |          |
|-----------------------------------|--------------|-----------------------------------|----------|
| Silicone                          | Yes          | Number of wires                   | 1        |
| O.D.                              | 36 mm        | Operating temperature range, max. | 90 °C    |
| Operating temperature range, min. | -30 °C       | Pitch of thread                   | 1.5 mm   |
| Thickness                         | 2.00 mm      | Cable gland                       | M 32     |
| Basic material                    | Polyethylene | Diameter of sealing ring          | 36.00 mm |
| Sealing                           | PE-HD        | External thread                   | M 32     |
| Internal thread                   | M 32         | Inside diameter D2                | 32.00 mm |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001181    | ETIM 9.0    | EC001181    |
| ETIM 10.0   | EC001181    | ECLASS 14.0 | 27-43-03-19 |
| ECLASS 15.0 | 27-43-03-19 |             |             |

**Drawings**

