

**GWDR M40-PO****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Version	GWDR PO (flat gasket - polyethylene), Sealing ring, M 40, Polyethylene
Order No.	<a href="#">1777970000</a>
Type	GWDR M40-PO
GTIN (EAN)	4032248158232
Qty.	50 items

**GWDR M40-PO**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Height	2 mm	Height (inches)	0.0787 inch
Net weight	0.66 g		

**Temperatures**

Operating temperature -30 °C...90 °C

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**General information**

Silicone	Yes	Number of wires	1
O.D.	45 mm	Operating temperature range, max.	90 °C
Operating temperature range, min.	-30 °C	Pitch of thread	1.5 mm
Thickness	2.00 mm	Cable gland	M 40
Basic material	Polyethylene	Diameter of sealing ring	45.00 mm
Sealing	PE-HD	External thread	M 40
Internal thread	M 40	Inside diameter D2	40.00 mm

**Classifications**

ETIM 8.0	EC001181	ETIM 9.0	EC001181
ETIM 10.0	EC001181	ECLASS 14.0	27-43-03-19
ECLASS 15.0	27-43-03-19		

**Drawings**

