

WTW WF10/WF12 2300

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image

Partition plates and end plates are essential accessories for terminal blocks. Partition plates provide optical and electrical separation of different potentials and functional groups, increasing safety and ensuring a clear structure inside the control cabinet. End plates close the terminal block row on the sides, protect against contact with live parts, and ensure a clean, stable finish. Both components are precisely matched to the respective Weidmüller terminal block series, contributing to safe, compliant, and professional wiring.

General ordering data

| | |
|------------|--|
| Version | Bolt-type screw terminals, Partition plate, grey, 2 mm |
| Order No. | 1780920000 |
| Type | WTW WF10/WF12 2300 |
| GTIN (EAN) | 4032248241149 |
| Qty. | 20 items |

WTW WF10/WF12 2300

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|----------------------------|----------|-----------------|-------------|
| Depth | 76.45 mm | Depth (inches) | 3.0098 inch |
| Height | 155.8 mm | Height (inches) | 6.1338 inch |
| Width | 2 mm | Width (inches) | 0.0787 inch |
| Mounting dimension - width | 2 mm | Net weight | 41.05 g |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|---------------|
| Storage temperature | -25 °C...55 °C | Ambient temperature | -5 °C...40 °C |
| Continuous operating temp., min. | -60 °C | Continuous operating temp., max. | 160 °C |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Material data

| | | | |
|---------------------------|-------------|--------|------|
| Basic material | Epoxy resin | Colour | grey |
| UL 94 flammability rating | V-0 | | |

System specifications

| | |
|---------|----------------------------|
| Version | End and intermediate plate |
|---------|----------------------------|

Additional technical data

| | | | |
|---------|----|---------------------|-----------------|
| Snap-on | No | Installation advice | Direct mounting |
|---------|----|---------------------|-----------------|

General

| | | | |
|---------------------|-----------------|-----------------------------------|--------|
| Installation advice | Direct mounting | Operating temperature range, max. | 160 °C |
|---------------------|-----------------|-----------------------------------|--------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000886 | ETIM 9.0 | EC000886 |
| ETIM 10.0 | EC000886 | ECLASS 14.0 | 27-25-03-01 |
| ECLASS 15.0 | 27-25-03-01 | | |

WTW WF10/WF12 2300

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Protection against contact



Our systems for touch protection ensure greater safety in your cabinet. They provide protection against electric shock caused by accidental contact with live parts due to operation or faults.

General ordering data

| | | | |
|------------|----------------------------|---------|--|
| Type | ADP WF10/WF12 | Version | |
| Order No. | 1780940000 | | |
| GTIN (EAN) | 4032248241255 | | Bolt-type screw terminals, Cover profile, Transparent, 1000 mm |
| Qty. | 1 M | | |