

ZBW 1/3.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image

We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

General ordering data

Version	Z-series, Operating tool
Order No.	1781930000
Type	ZBW 1/3.5
GTIN (EAN)	4032248199532
Qty.	1 items

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	23.75 mm	Depth (inches)	0.935 inch
Height	140.7 mm	Height (inches)	5.5394 inch
Width	27.76 mm	Width (inches)	1.0929 inch
Net weight	16.52 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-40 °C...55 °C
Continuous operating temp., min.	-40 °C	Continuous operating temp., max.	100 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	POM	Colour	orange
UL 94 flammability rating	HB		

System specifications

Version	Operating tool
---------	----------------

Additional technical data

Explosion-tested version	No
--------------------------	----

Classifications

ETIM 8.0	EC000149	ETIM 9.0	EC000149
ETIM 10.0	EC000149	ECLASS 14.0	21-04-50-03
ECLASS 15.0	21-04-50-03		