

SM 27/27 K MC SDR


Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration



SM is a MultiCard marker for labelling control and signalling devices. The tags are clipped into the carriers or attached by means of the adhesive film already fitted to them. Customised tags can be created with the PrintJet CONNECT or Plotter marking systems.

- Users can quickly produce tags to suit their needs
- No need to stock expensive standard tags
- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- For extreme demands, we recommend the ETO SM protective film
- Holders can be used for the 22-mm or 30-mm-diameter push-buttons from Siemens, ABB, Moeller and Télémécanique

For custom printing: Please send us a file of our labelling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Version	SwitchMark, Device markers, 27 x 27 mm, To customer specification
Order No.	1783010000
Type	SM 27/27 K MC SDR
GTIN (EAN)	4032248180073
Qty.	12 items

SM 27/27 K MC SDR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	1 mm	Depth (inches)	0.0394 inch
Height	27 mm	Height (inches)	1.063 inch
Width	27 mm	Width (inches)	1.063 inch
Net weight	1.42 g		

Temperatures

Operating temperature range -40...60 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Product Carbon Footprint	Cradle to gate	0.013 kg CO2 eq.	

General data

Adhesive	Double-sided adhesive tape		
Printing method	MC Laser		
Version	Self-adhesive		
Width	27 mm		
UL 94 flammability rating	V-2		
Operating temperature range, max.	60 °C		
Operating temperature range, min.	-40 °C		
Colour	To customer specification		
Halogen	No		
Basic material	Polyamide 66		
Colour of printing	black		
Printed characters	Requires M-Print PRO File		
Number of markers per packaging unit	Form of supply	MultiCard	
compatible printer	PRINTJET CONNECT , MCP BASIC 2 , MCP PLUS 2		
Number of markers per combination	1 MultiCard = Device markers		
Operating temperature range	-40...60 °C		

Device markers

Halogen No

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

SM 27/27 K MC SDR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Complementary products



SM is a MultiCard marker for labelling control and signalling devices. The tags are clipped into the carriers or attached by means of the adhesive film already fitted to them. Customised tags can be created with the PrintJet CONNECT or Plotter marking systems.

- Users can quickly produce tags to suit their needs
- No need to stock expensive standard tags
- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- For extreme demands, we recommend the ETO SM protective film
- Holders can be used for the 22-mm or 30-mm-diameter push-buttons from Siemens, ABB, Moeller and Télémécanique

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	ETO SM 27/27	Version	
Order No.	1805840000	SwitchMark, Protective cap, 27 x 27 mm, Transparent	
GTIN (EAN)	4032248273577		
Qty.	10 ST		