

HDC 64D TOLU 1M25G
Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

Version	HDC enclosures, Installation size: 8, Protection degree: IP65, in plugged condition, Cable entry from top, Plug housing, End-locking clamp, lower side, high, Size of cable entries: M 25
Order No.	1786870000
Type	HDC 64D TOLU 1M25G
GTIN (EAN)	4032248204113
Qty.	1 items

HDC 64D TOLU 1M25G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E92202

Dimensions and weights

Height	76 mm	Height (inches)	2.9921 inch
Width	45.5 mm	Width (inches)	1.7913 inch
Net weight	308 g		

Temperatures

Limit temperature	-40 °C ... 125 °C
-------------------	-------------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption	
REACH SVHC	No SVHC above 0.1 wt%	
Chemical resistance	Substance	Acetone
	Chemical resistance	Conditionally resistant
	Substance	Drilling oil
	Chemical resistance	Resistant
	Substance	Diesel
	Chemical resistance	Resistant
	Substance	Ethyl alcohol
	Chemical resistance	Resistant
	Substance	Transmission oil
	Chemical resistance	Resistant
	Substance	Hydraulic oil
	Chemical resistance	Resistant
	Substance	Coolant
	Chemical resistance	Resistant
	Substance	Petroleum benzine
	Chemical resistance	Resistant
	Substance	Sweat
	Chemical resistance	Resistant
	Substance	Premium gasoline
	Chemical resistance	Conditionally resistant
Substance	Water	
Chemical resistance	Resistant	
Substance	UV	
Chemical resistance	Unstable	
Substance	Ozone	
Chemical resistance	Unstable	

Dimensions

Cable entry	w. thread	Width housing C	43 mm
Total length housing	120 mm	Height of housing B	76 mm

HDC 64D TOLU 1M25G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

General data

Housing main material	diecast aluminium	Surface finish	Powder coating
Protection degree	IP65, in plugged condition	EMC housings	No
Material of locking element	Stainless steel, rust-proof		

Version

Size of cable entries	M 25	Top part/bottom part/lid	upper part
Cover	without cover	Number of cable entry on top	1
Number of cable entry sideways	0	Design of housing	Cable entry from top, Plug housing
Design of locking system	End-locking clamp, lower side	Design	high
Installation size	8	Cable entry	w. thread
Type	Plug	Clamp version	End-locking clamp
Sealing	no sealing	Internal thread	M 25
Colour (RAL)	RAL 7035	BG	8
Suitable for ModuPlug®	Yes		

Classifications

ETIM 8.0	EC000437	ETIM 9.0	EC000437
ETIM 10.0	EC000437	ECLASS 14.0	27-44-02-02
ECLASS 15.0	27-44-02-02		

HDC 64D TOLU 1M25G

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com



HDC 64D TOLU 1M25G

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Accessories

www.weidmueller.com

Base housing



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

Type	HDC 24B SDLU 2PG21G	Version
Order No.	1214500000	HDC enclosures, Installation size: 8, Protection degree: IP65, in plugged condition, Base housing, End-locking clamp, lower side, Standard, with cover, Size of cable entries: PG 21
GTIN (EAN)	4008190153021	
Qty.	1 ST	
Type	HDC 24B SLU 2PG21G	Version
Order No.	1662720000	HDC enclosures, Installation size: 8, Protection degree: IP65, in plugged condition, Base housing, End-locking clamp, lower side, Standard, Size of cable entries: PG 21
GTIN (EAN)	4008190419240	
Qty.	1 ST	
Type	HDC 64D SDLU 2PG29G	Version
Order No.	1663040000	HDC enclosures, Installation size: 8, Protection degree: IP65, in plugged condition, Base housing, End-locking clamp, lower side, high, with cover, Size of cable entries: PG 29
GTIN (EAN)	4008190419561	
Qty.	1 ST	
Type	HDC 64D SLU 2M32G	Version
Order No.	1786900000	HDC enclosures, Installation size: 8, Protection degree: IP65, in plugged condition, Base housing, End-locking clamp, lower side, high, Size of cable entries: M 32
GTIN (EAN)	4032248204144	
Qty.	1 ST	
Type	HDC 64D SLU 2M25G	Version
Order No.	1786910000	HDC enclosures, Installation size: 8, Protection degree: IP65, in plugged condition, Base housing, End-locking clamp, lower side, high, Size of cable entries: M 25
GTIN (EAN)	4032248204151	
Qty.	1 ST	
Type	HDC 64D SDLU 2M32G	Version
Order No.	1786940000	HDC enclosures, Installation size: 8, Protection degree: IP65, in plugged condition, Base housing, End-locking clamp, lower side, high, with cover, Size of cable entries: M 32
GTIN (EAN)	4032248204182	
Qty.	1 ST	
Type	HDC 64D SDLU 2M25G	Version
Order No.	1786950000	HDC enclosures, Installation size: 8, Protection degree: IP65, in plugged condition, Base housing, End-locking clamp, lower side, high, with cover, Size of cable entries: M 25
GTIN (EAN)	4032248204199	
Qty.	1 ST	
Type	HDC 24B SLU 2M25G	Version
Order No.	1787880000	HDC enclosures, Installation size: 8, Protection degree: IP65, in plugged condition, Base housing, End-locking clamp, lower side, Standard, Size of cable entries: M 25
GTIN (EAN)	4032248205325	
Qty.	1 ST	

HDC 64D TOLU 1M25G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Type	HDC 24B SDLU 2M25G	Version
Order No.	1787900000	HDC enclosures, Installation size: 8, Protection degree: IP65, in plugged condition, Base housing, End-locking clamp, lower side, Standard, with cover, Size of cable entries: M 25
GTIN (EAN)	4032248205349	
Qty.	1 ST	
Type	HDC 24B SDLU 1M25G	Version
Order No.	1901480000	HDC enclosures, Installation size: 8, Protection degree: IP65, in plugged condition, Base housing, End-locking clamp, lower side, Standard, with cover, Size of cable entries: M 25
GTIN (EAN)	4032248521364	
Qty.	1 ST	
Type	HDC 24B SLU 1M25G	Version
Order No.	1901560000	HDC enclosures, Installation size: 8, Protection degree: IP65, in plugged condition, Base housing, End-locking clamp, lower side, Standard, Size of cable entries: M 25
GTIN (EAN)	4032248521395	
Qty.	1 ST	
Type	HDC 64D SDLU 1M25G	Version
Order No.	1904430000	HDC enclosures, Installation size: 8, Protection degree: IP65, in plugged condition, Base housing, End-locking clamp, lower side, high, with cover, Size of cable entries: M 25
GTIN (EAN)	4032248585106	
Qty.	1 ST	
Type	HDC 64D SDLU 1M32G	Version
Order No.	1904440000	HDC enclosures, Installation size: 8, Protection degree: IP65, in plugged condition, Base housing, End-locking clamp, lower side, high, with cover, Size of cable entries: M 32
GTIN (EAN)	4032248585212	
Qty.	1 ST	
Type	HDC 64D SLU 1M25G	Version
Order No.	1904480000	HDC enclosures, Installation size: 8, Protection degree: IP65, in plugged condition, Base housing, End-locking clamp, lower side, high, Size of cable entries: M 25
GTIN (EAN)	4032248585090	
Qty.	1 ST	
Type	HDC 64D SLU 1M32G	Version
Order No.	1904490000	HDC enclosures, Installation size: 8, Protection degree: IP65, in plugged condition, Base housing, End-locking clamp, lower side, high, Size of cable entries: M 32
GTIN (EAN)	4032248585618	
Qty.	1 ST	

Bulkhead housing



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

Type	HDC 24B ALU	Version
Order No.	1213900000	HDC enclosures, Installation size: 8, Protection degree: IP65, in plugged condition, Bulkhead housing, End-locking clamp, lower side, Standard, Size of cable entries: none
GTIN (EAN)	4008190176303	
Qty.	1 ST	

HDC 64D TOLU 1M25G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Type	HDC 24B ADLU	Version
Order No.	1214300000	HDC enclosures, Installation size: 8, Protection degree: IP65, in
GTIN (EAN)	4008190083090	plugged condition, Bulkhead housing, End-locking clamp, lower side,
Qty.	1 ST	Standard, with cover, Size of cable entries: none

Coupling hood



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

Type	HDC 24B KLU 1M25G	Version
Order No.	1968340000	HDC enclosures, Installation size: 8, Protection degree: IP65, in
GTIN (EAN)	4032248689378	plugged condition, Coupling housing, End-locking clamp, lower side,
Qty.	1 ST	Standard, Size of cable entries: M 25