

WSH 26 MT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The comprehensive accessories of the Klippon® Connect portfolio are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms

General ordering data

Version	Accessories, metal
Order No.	1789750000
Type	WSH 26 MT
GTIN (EAN)	40322482 13603
Qty.	10 items

WSH 26 MT

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	134 mm	Depth (inches)	5.2756 inch
Height	32.8 mm	Height (inches)	1.2913 inch
Width	14.8 mm	Width (inches)	0.5827 inch
Net weight	52.5 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
Continuous operating temp., max.	85 °C		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	metal	Colour	grey
UL 94 flammability rating	None		

Additional technical data

Explosion-tested version	No	Type of mounting	when screwed in
--------------------------	----	------------------	-----------------

General

Number of poles	1
-----------------	---

Classifications

ETIM 8.0	EC001166	ETIM 9.0	EC001166
ETIM 10.0	EC001166	ECLASS 14.0	27-40-06-07
ECLASS 15.0	27-40-06-07		