

SAI-4/6/8-MHF 4P PUR 9M**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



M12 distributors are available in various versions. The 4, 6 or 8 M12 slots are in 4 or 5 pole design. The group outlet is designed as a fixed cable version, hood version for connection by the user, or with M23. Special versions are also available. For instance, there are 1-to-1 distributors for use with any connection types, or distributors approved for Ex Zone 1.

General ordering data

Version	Hood version, 30 V, , LED: No, LED initiator: No, Wiring type: None, 9 m
Order No.	1791450900
Type	SAI-4/6/8-MHF 4P PUR 9M
GTIN (EAN)	4032248221134
Qty.	1 items
Delivery status	Discontinued
Last order date	2025-12-30T00:00:00+01:00
Alternative product	SAI-4/6/8-MHF 4P PUR15M

SAI-4/6/8-MHF 4P PUR 9M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	59.2 mm	Depth (inches)	2.3307 inch
Height	32.5 mm	Height (inches)	1.2795 inch
Net weight	965 g		

Temperatures

Operating temperature	-20 - 80°C
-----------------------	------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Connection data

Cable gland	M 20	Distributor outlet	Hood version
-------------	------	--------------------	--------------

Electrical data

Rated voltage, min.	10 V	Rated voltage, max.	30 V
Max. current-carrying capacity per slot	4 A	Total current	10 A
Electrical isolation available	No		

General technical data

Protection degree	IP68	Number of poles	4
Pollution severity	3	LED	No
LED initiator	No		

Material data

Housing main material	Pocan	Material of distributor	Plastic
Housing colour	grey, RAL 7032	Contact material	CuZn
Contact surface	Gold-plated	Contact carrier material	PBT (UL 94 V0)

Technical data cable

Number of poles	4	Sheathing colour	black
O.D.	8.2 mm	Shielded	No
Halogen	No	Bending radius, min., moving	10 x cable diameter
Bending cycles	2 Mio	Sheath material	PUR
Colour coding	white, green, yellow, grey, pink, red, brown, black, violet, grey / pink, red / blue, white / green, white / yellow, Yellow / brown, white / grey, grey / brown, blue, Green/yellow	Cable length	9 m
Suitable for cable carriers	Yes		

SAI-4/6/8-MHF 4P PUR 9M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Classifications

ETIM 8.0	EC002585	ETIM 9.0	EC002585
ETIM 10.0	EC002585	ECLASS 14.0	27-44-01-08
ECLASS 15.0	27-44-01-08		