

SKMU M12 K SW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

| | |
|------------|---|
| Version | SKMU PA (plastic locknut), Locknut, M 12, 5 mm, Polyamid 6 (PA6 - GF30) |
| Order No. | 1806540000 |
| Type | SKMU M12 K SW |
| GTIN (EAN) | 4032248276493 |
| Qty. | 100 items |

SKMU M12 K SW

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Height | 5 mm | Height (inches) | 0.1968 inch |
| Net weight | 1.09 g | | |

Temperatures

Operating temperature -40 °C...100 °C

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

General information

| | | | |
|-----------------------------------|-------------------------|-----------------------------------|----------|
| Silicone | No | O.D. | 20.79 mm |
| UL 94 flammability rating | HB | Operating temperature range, max. | 100 °C |
| Operating temperature range, min. | -40 °C | Pitch of thread | 1.5 mm |
| Halogen | No | AF size 1 | 18 mm |
| Thickness | 5.00 mm | Cable gland | M 12 |
| Basic material | Polyamid 6 (PA6 - GF30) | External thread | M 12 |
| Internal thread | M 12 x 1.5 | Length of thread | 5 mm |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000940 | ETIM 9.0 | EC000940 |
| ETIM 10.0 | EC000940 | ECLASS 14.0 | 27-14-08-07 |
| ECLASS 15.0 | 27-14-08-07 | | |