


**ZZE ZP2.5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

The plugs for our WeiCoS-System are available for all different connection systems. The product range includes preassembled connectors from 1 to 10 poles and the possibility of an individual assembly. This ensures maximum flexibility for every application. The customized accessories increase the safety and protection against environmental influences.

**General ordering data**

Version	Z-series, Strain relief, yellow, 9.9 mm
Order No.	<a href="#">1816140000</a>
Type	ZZE ZP2.5
GTIN (EAN)	4032248370719
Qty.	25 items

## ZZE ZP2.5

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS Conform

## Dimensions and weights

Depth	7.87 mm	Depth (inches)	0.3098 inch
Height	53 mm	Height (inches)	2.0866 inch
Width	9.9 mm	Width (inches)	0.3898 inch
Net weight	0.84 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-50 °C...55 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Material data

Basic material	PA 66 GF 30	Colour	yellow
UL 94 flammability rating	HB		

## System specifications

Version Strain relief

## Additional technical data

Installation advice Direct mounting

## General

Installation advice Direct mounting

## Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		