


WQV 50N/4**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

General ordering data

| | |
|------------|---|
| Version | Cross-connector (terminal), when screwed in, Silver grey, 150 A, Number of poles: 4, Pitch in mm (P): 18.50, Insulated: No, Width: 9.5 mm |
| Order No. | 1834080000 |
| Type | WQV 50N/4 |
| GTIN (EAN) | 4032248379873 |
| Qty. | 5 items |

WQV 50N/4

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 17.5 mm | Depth (inches) | 0.689 inch |
| Height | 65.5 mm | Height (inches) | 2.5787 inch |
| Width | 9.5 mm | Width (inches) | 0.374 inch |
| Net weight | 63.9 g | | |

Temperatures

| | | | |
|---------------------|----------------|---------------------|---------------|
| Storage temperature | -25 °C...55 °C | Ambient temperature | -5 °C...40 °C |
|---------------------|----------------|---------------------|---------------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Material data

| | | | |
|----------------|---------------|--------|-------------|
| Basic material | tinned copper | Colour | Silver grey |
|----------------|---------------|--------|-------------|

System specifications

| | |
|---------|-------------------|
| Version | For the terminals |
|---------|-------------------|

Additional technical data

| | | | |
|--------------------------|-----------------|---------------------|-----------------|
| Type of fixing | when screwed in | Installation advice | Direct mounting |
| Explosion-tested version | No | | |

Dimensions

| | |
|-----------------|----------|
| Pitch in mm (P) | 18.50 mm |
|-----------------|----------|

General

| | | | |
|-----------------|---|---------------------|-----------------|
| Number of poles | 4 | Installation advice | Direct mounting |
|-----------------|---|---------------------|-----------------|

Rating data

| | | | |
|---------------|-------|-----------------|-------|
| Rated voltage | 400 V | Nominal current | 150 A |
|---------------|-------|-----------------|-------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000489 | ETIM 9.0 | EC000489 |
| ETIM 10.0 | EC000489 | ECLASS 14.0 | 27-25-03-03 |
| ECLASS 15.0 | 27-25-03-03 | | |

WQV 50N/4

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

auxiliary connection



The additional connection enables a separate voltage tap. This can be used, for example, for the emergency power supply before the main switch or simply as an additional connection within the application.

General ordering data

| | | | |
|------------|----------------------------|-------------------------|--|
| Type | VH 27.4/8/6.4 | Version | |
| Order No. | 1967090000 | W-Series, Spacer sleeve | |
| GTIN (EAN) | 4032248738700 | | |
| Qty. | 5 ST | | |