

**STB 36.8/IH/BL WTL6/1**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Product image****Current and voltage transformer wiring**

Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

**General ordering data**

Version	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 39.8 mm
Order No.	<a href="#">1847790000</a>
Type	STB 36.8/IH/BL WTL6/1
GTIN (EAN)	4032248379149
Qty.	50 items

## STB 36.8/IH/BL WTL6/1

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	39.8 mm	Depth (inches)	1.5669 inch
Height	36.8 mm	Height (inches)	1.4488 inch
Width	6 mm	Width (inches)	0.2362 inch
Net weight	4.86 g		

### Temperatures

Ambient temperature	-5 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

### Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	dce63e23-eea1-4eaa-9071-1c98fc8fa2ea

### Material data

Basic material	Polyamide 66	Colour	blue
UL 94 flammability rating	V-2		

### System specifications

Version	For the terminals
---------	-------------------

### Additional technical data

Type of fixing	when screwed in	Installation advice	Direct mounting
Explosion-tested version	No	Type of mounting	when screwed in

### Dimensions

Plug-in depth	11.1 mm	TS 35 offset	47 mm
---------------	---------	--------------	-------

### General

Installation advice	Direct mounting	Operating temperature range, max.	100 °C
---------------------	-----------------	-----------------------------------	--------

### Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		