

CBFP 43.5/10 BK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Fastening of cables or bundles with ties into electrical switchgears and cabinets.

General ordering data

Version	Cable ties, 10 x 10 mm, Plastic, 80 N
Order No.	1859410000
Type	CBFP 43.5/10 BK
GTIN (EAN)	4032248412297
Qty.	100 items

CBFP 43.5/10 BK

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	2 mm	Depth (inches)	0.0787 inch
Height	10 mm	Height (inches)	0.3937 inch
Width	10 mm	Width (inches)	0.3937 inch
Net weight	1.91 g		

Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Installation materials

Max. cable tie width	9 mm	UV-resistant	No
For re-opening	No	Version	for wall mounting
UL 94 flammability rating	V-2	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Halogen	No
Basic material	Plastic	Tensile strength	80 N
Tensile strength (Pound-force)	18 lbf	Diameter of fastening hole	8 mm

Classifications

ETIM 8.0	EC000046	ETIM 9.0	EC000046
ETIM 10.0	EC000046	ECLASS 14.0	27-14-07-02
ECLASS 15.0	27-14-07-02		

Drawings

Dimensional drawing

