


**ZPS 2.5/1AN/QV/1****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

The plugs for our WeiCoS-System are available for all different connection systems. The product range includes preassembled connectors from 1 to 10 poles and the possibility of an individual assembly. This ensures maximum flexibility for every application. The customized accessories increase the safety and protection against environmental influences.

**General ordering data**

|            |  |
|------------|--|
| Version    | Z-series, Coupling, Rated cross-section: 2.5 mm <sup>2</sup> , Plug-in connection, Direct mounting |
| Order No.  | <a href="#">1861040000</a>   |
| Type       | ZPS 2.5/1AN/QV/1   |
| GTIN (EAN) | 4032248418435  |
| Qty.       | 50 items   |

## ZPS 2.5/1AN/QV/1

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



|                         |                            |
|-------------------------|----------------------------|
| ROHS                    | Conform                    |
| UL File Number Search   | <a href="#">UL Website</a> |
| Certificate No. (cURus) | E60693                     |

## Dimensions and weights

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 42 mm   | Depth (inches)  | 1.6535 inch |
| Height     | 28.1 mm | Height (inches) | 1.1063 inch |
| Width      | 5.1 mm  | Width (inches)  | 0.2008 inch |
| Net weight | 3.8 g   |                 |             |

## Temperatures

|                                  |                |                                  |               |
|----------------------------------|----------------|----------------------------------|---------------|
| Storage temperature              | -25 °C...55 °C | Ambient temperature              | -5 °C...40 °C |
| Continuous operating temp., min. | -50 °C         | Continuous operating temp., max. | 120 °C        |

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## Material data

|                           |       |        |            |
|---------------------------|-------|--------|------------|
| Basic material            | Wemid | Colour | dark beige |
| UL 94 flammability rating | V-0   |        |            |

## System specifications

|                                     |  |                                   |    |
|-------------------------------------|--|-----------------------------------|----|
| Version                             | Plug-in connector, pluggable, Tension-clamp connection | End cover plate required          | No |
| Number of potentials                | 1  | Number of levels                  | 1  |
| Number of clamping points per level | 1  | Levels cross-connected internally | No |
| PE connection                       | No   |                                   |    |

## Additional technical data

|                     |                 |                          |    |
|---------------------|-----------------|--------------------------|----|
| Installation advice | Direct mounting | Explosion-tested version | No |
| Type of mounting    | Direct mounting |                          |    |

## CSA rating data

|                               |        |                       |                |
|-------------------------------|--------|-----------------------|----------------|
| Wire cross section max. (CSA) | 12 AWG | Voltage size C (CSA)  | 300 V          |
| Current size C (CSA)          | 20 A   | Certificate No. (CSA) | 200039-1720292 |
| Voltage size D (CSA)          | 600 V  | Current size D (CSA)  | 5 A            |
| Wire cross section min. (CSA) | 26 AWG |                       |                |

**ZPS 2.5/1AN/QV/1****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)
**Technical data****Conductors for clamping (rated connection)**

|   |                      |   |                      |
|---|----------------------|---|----------------------|
| Gauge to IEC 60947-1  | A2                   | Wire connection cross section AWG, max.   | AWG 12               |
| Connection direction  | top                  | Stripping length  | 10 mm                |
| Type of connection  | Plug-in connection   | Number of connections   | 1                    |
| Clamping range, max.  | 4 mm <sup>2</sup>    | Clamping range, min.  | 0.13 mm <sup>2</sup> |
| Blade size  | 0.6 x 3.5 mm         | Wire connection cross section AWG, min.   | AWG 26               |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.13 mm <sup>2</sup> | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 2.5 mm <sup>2</sup>  |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.13 mm <sup>2</sup> | Wire connection cross section, finely stranded, max.                                    | 4 mm <sup>2</sup>    |
| Wire connection cross section, finely stranded, min.                                    | 0.13 mm <sup>2</sup> | Connection cross-section, stranded, min.  | 0.13 mm <sup>2</sup> |
| Wire connection cross-section, solid core, max.   | 4 mm <sup>2</sup>    | Wire connection cross-section, solid core, min.   | 0.13 mm <sup>2</sup> |

**General**

|                     |                          |   |        |
|---------------------|--------------------------|---|--------|
| Number of poles     | 1                        | Wire connection cross section AWG, max. | AWG 12 |
| Installation advice | Direct mounting          | Wire connection cross section AWG, min. | AWG 26 |
| Standards           | IEC 60947-7-1, IEC 61984 |   |        |

**Rating data**

|  |                     |                                 |                          |
|--|---------------------|---------------------------------|--------------------------|
| Rated cross-section                          | 2.5 mm <sup>2</sup> | Rated voltage                   | 500 V                    |
| Rated DC voltage                             | 500 V               | Nominal current                 | 24 A                     |
| Current at maximum wires                     | 24 A                | Standards                       | IEC 60947-7-1, IEC 61984 |
| Volume resistance according to IEC 60947-7-x | 1.33 mΩ             | Rated impulse withstand voltage | 6 kV                     |
| Power loss in accordance with IEC 60947-7-x  | 0.77 W              | Pollution severity              | 3                        |

**UL rating data**

|  |        |  |        |
|--|--------|--|--------|
| Conductor size Factory wiring max. (cURus) | 12 AWG | Voltage size D (cURus)                   | 600 V  |
| Certificate No. (cURus)                    | E60693 | Conductor size Field wiring min. (cURus) | 26 AWG |
| Conductor size Factory wiring min. (cURus) | 26 AWG | Voltage size C (cURus)                   | 300 V  |
| Current size C (cURus)                     | 24 A   | Current size D (cURus)                   | 5 A    |
| Conductor size Field wiring max. (cURus)   | 12 AWG |  |        |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002848    | ETIM 7.0    | EC002848    |
| ETIM 8.0    | EC002848    | ETIM 9.0    | EC002848    |
| ETIM 10.0   | EC002848    | ECLASS 9.0  | 27-14-11-92 |
| ECLASS 9.1  | 27-14-11-92 | ECLASS 10.0 | 27-14-11-92 |
| ECLASS 11.0 | 27-14-11-92 | ECLASS 12.0 | 27-14-11-92 |
| ECLASS 13.0 | 27-25-03-90 | ECLASS 14.0 | 27-25-03-90 |
| ECLASS 15.0 | 27-25-03-90 |             |             |

## ZPS 2.5/1AN/QV/1

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Cross-connections



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

## General ordering data

|            |                            |                                 |
|------------|----------------------------|---------------------------------|
| Type       | ZQV 2.5N/20 GE             | Version                         |
| Order No.  | <a href="#">1909000000</a> | W-Series, Cross-connector, 24 A |
| GTIN (EAN) | 4032248535613              |                                 |
| Qty.       | 20 ST                      |                                 |

## Testadapter and testsockets



Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

## General ordering data

|            |                            |                                   |
|------------|----------------------------|-----------------------------------|
| Type       | ZTA ZT2.5                  | Version                           |
| Order No.  | <a href="#">1827080000</a> | Accessories, Test adapter, 17.5 A |
| GTIN (EAN) | 4032248411276              |                                   |
| Qty.       | 25 ST                      |                                   |
| Type       | ZTA ZT2.5/ZA               | Version                           |
| Order No.  | <a href="#">1847600000</a> | Accessories, Test adapter, 17.5 A |
| GTIN (EAN) | 4032248412679              |                                   |
| Qty.       | 25 ST                      |                                   |

## Slotted screwdriver



Slotted screwdriver with rounded blade SD DIN 5265, ISO 2380/2, output to DIN 5264, ISO 2380/1. ChromTop tip, SoftFinish grip

## ZPS 2.5/1AN/QV/1

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## General ordering data

|            |                            |                          |  |
|------------|----------------------------|--------------------------|--|
| Type       | SDS 0.6X3.5X100            | Version                  |  |
| Order No.  | <a href="#">9008330000</a> | Screwdriver, Screwdriver |  |
| GTIN (EAN) | 4032248056286              |                          |  |
| Qty.       | 1 ST                       |                          |  |

## Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.


Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
  - Strips for fast installation
  - Terminal markers, suitable for all Weidmüller cable connectors
  - Available as blank MultiCard or with standard printing
- For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

|            |                            |  |  |
|------------|----------------------------|--|--|
| Type       | DEK 5/5 MC NE WS           | Version  |  |
| Order No.  | <a href="#">1609801044</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00          |  |
| GTIN (EAN) | 4008190397111              | Weidmueller, white   |  |
| Qty.       | 1000 ST                    |  |  |
| Type       | WS 10/5 MC NE WS           | Version  |  |
| Order No.  | <a href="#">1635000000</a> | WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |  |
| GTIN (EAN) | 4008190261948              | Allen-Bradley, white   |  |
| Qty.       | 720 ST                     |  |  |
| Type       | ZS 10/5 MC NE WS           | Version  |  |
| Order No.  | <a href="#">1610000000</a> | ZS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |  |
| GTIN (EAN) | 4008190263171              | Allen-Bradley, white   |  |
| Qty.       | 480 ST                     |  |  |

## Marker holder



The marker holder offer the possibility of additional mounting of standard markers with a pitch of 5 or 5.1 mm. The angled holders can be optionally snapped together and could be mounted in all standard marking channels of the Klippon® Connect modular terminal blocks. Fitting marker types could be found under the respective accessories of the designation marking holder.

## ZPS 2.5/1AN/QV/1

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## General ordering data

|            |                            |                            |
|------------|----------------------------|----------------------------|
| Type       | BZT 1 WS 10/5              | Version                    |
| Order No.  | <a href="#">1805490000</a> | Accessories, Marker holder |
| GTIN (EAN) | 4032248270231              |                            |
| Qty.       | 100 ST                     |                            |
| Type       | BZT 1 ZA WS 10/5           | Version                    |
| Order No.  | <a href="#">1805520000</a> | Accessories, Marker holder |
| GTIN (EAN) | 4032248270248              |                            |
| Qty.       | 100 ST                     |                            |

## Cross-connections



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | ZQV 2.5/10                 | Version   |
| Order No.  | <a href="#">1608940000</a> | Accessories, Cross-connector, 24 A                                |
| GTIN (EAN) | 4008190099060              |   |
| Qty.       | 20 ST                      |   |
| Type       | ZQV 2.5/10 RT              | Version   |
| Order No.  | <a href="#">2714770000</a> | Z-series, Cross-connector, For the terminals, Number of poles: 10 |
| GTIN (EAN) | 4050118765106              |   |
| Qty.       | 20 ST                      |   |
| Type       | ZQV 2.5/11                 | Version   |
| Order No.  | <a href="#">1859080000</a> | Z-series, Cross-connector, For the terminals, Number of poles: 11 |
| GTIN (EAN) | 4032248411047              |   |
| Qty.       | 20 ST                      |   |
| Type       | ZQV 2.5/2                  | Version   |
| Order No.  | <a href="#">1608860000</a> | Z-series, Cross-connector, 24 A                                   |
| GTIN (EAN) | 4008190123680              |   |
| Qty.       | 60 ST                      |   |
| Type       | ZQV 2.5/2 RT               | Version   |
| Order No.  | <a href="#">2714780000</a> | Z-series, Cross-connector, For the terminals, Number of poles: 2  |
| GTIN (EAN) | 4050118765014              |   |
| Qty.       | 60 ST                      |   |
| Type       | ZQV 2.5/20                 | Version   |
| Order No.  | <a href="#">1908960000</a> | Z-series, Cross-connector, For the terminals, Number of poles: 20 |
| GTIN (EAN) | 4032248535293              |   |
| Qty.       | 20 ST                      |   |
| Type       | ZQV 2.5/20 RT              | Version   |
| Order No.  | <a href="#">2714860000</a> | Z-series, Cross-connector, For the terminals, Number of poles: 20 |
| GTIN (EAN) | 4050118764383              |   |
| Qty.       | 20 ST                      |   |

## ZPS 2.5/1AN/QV/1

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

|            |                            |  |
|------------|----------------------------|--|
| Type       | ZQV 2.5/3                  | Version  |
| Order No.  | <a href="#">1608870000</a> | Accessories, Cross-connector, 24 A                               |
| GTIN (EAN) | 4008190061630              |  |
| Qty.       | 60 ST                      |  |
| Type       | ZQV 2.5/3 RT               | Version  |
| Order No.  | <a href="#">2714790000</a> | Z-series, Cross-connector, For the terminals, Number of poles: 3 |
| GTIN (EAN) | 4050118764390              |  |
| Qty.       | 60 ST                      |  |
| Type       | ZQV 2.5/4                  | Version  |
| Order No.  | <a href="#">1608880000</a> | Accessories, Cross-connector, 24 A                               |
| GTIN (EAN) | 4008190082208              |  |
| Qty.       | 60 ST                      |  |
| Type       | ZQV 2.5/4 RT               | Version  |
| Order No.  | <a href="#">2714800000</a> | Z-series, Cross-connector, For the terminals, Number of poles: 4 |
| GTIN (EAN) | 4050118765007              |  |
| Qty.       | 60 ST                      |  |
| Type       | ZQV 2.5/5                  | Version  |
| Order No.  | <a href="#">1608890000</a> | Accessories, Cross-connector, 24 A                               |
| GTIN (EAN) | 4008190065713              |  |
| Qty.       | 20 ST                      |  |
| Type       | ZQV 2.5/5 RT               | Version  |
| Order No.  | <a href="#">2714810000</a> | Z-series, Cross-connector, For the terminals, Number of poles: 5 |
| GTIN (EAN) | 4050118764994              |  |
| Qty.       | 20 ST                      |  |
| Type       | ZQV 2.5/50                 | Version  |
| Order No.  | <a href="#">1697540000</a> | Accessories, Cross-connector, 24 A                               |
| GTIN (EAN) | 4008190883256              |  |
| Qty.       | 10 ST                      |  |
| Type       | ZQV 2.5/6                  | Version  |
| Order No.  | <a href="#">1608900000</a> | Accessories, Cross-connector, 24 A                               |
| GTIN (EAN) | 4008190149840              |  |
| Qty.       | 20 ST                      |  |
| Type       | ZQV 2.5/6 RT               | Version  |
| Order No.  | <a href="#">2714820000</a> | Z-series, Cross-connector, For the terminals, Number of poles: 6 |
| GTIN (EAN) | 4050118764987              |  |
| Qty.       | 20 ST                      |  |
| Type       | ZQV 2.5/7                  | Version  |
| Order No.  | <a href="#">1608910000</a> | Accessories, Cross-connector, 24 A                               |
| GTIN (EAN) | 4008190159665              |  |
| Qty.       | 20 ST                      |  |
| Type       | ZQV 2.5/7 RT               | Version  |
| Order No.  | <a href="#">2714830000</a> | Z-series, Cross-connector, For the terminals, Number of poles: 7 |
| GTIN (EAN) | 4050118764970              |  |
| Qty.       | 20 ST                      |  |
| Type       | ZQV 2.5/8                  | Version  |
| Order No.  | <a href="#">1608920000</a> | Accessories, Cross-connector, 24 A                               |
| GTIN (EAN) | 4008190061531              |  |
| Qty.       | 20 ST                      |  |
| Type       | ZQV 2.5/8 RT               | Version  |
| Order No.  | <a href="#">2714840000</a> | Z-series, Cross-connector, For the terminals, Number of poles: 8 |
| GTIN (EAN) | 4050118762198              |  |
| Qty.       | 20 ST                      |  |

**ZPS 2.5/1AN/QV/1****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories**

|            |                            |  |
|------------|----------------------------|--|
| Type       | ZQV 2.5/9                  | Version  |
| Order No.  | <a href="#">1608930000</a> | Accessories, Cross-connector, 24 A                               |
| GTIN (EAN) | 4008190117009              |  |
| Qty.       | 20 ST                      |  |
| Type       | ZQV 2.5/9 RT               | Version  |
| Order No.  | <a href="#">2714850000</a> | Z-series, Cross-connector, For the terminals, Number of poles: 9 |
| GTIN (EAN) | 4050118764963              |  |
| Qty.       | 20 ST                      |  |