

**CLI C 1-6 GE/SW 52 CD****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Similar to illustration

CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm<sup>2</sup> to max. 70 mm<sup>2</sup>. The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

**General ordering data**

|                 |                                                                        |
|-----------------|------------------------------------------------------------------------|
| Version         | CableLine, Conductor and cable markers, 2.5 - 5 mm, 6 x 4.2 mm, yellow |
| Order No.       | <a href="#">1868811573</a>                                             |
| Type            | CLI C 1-6 GE/SW 52 CD                                                  |
| GTIN (EAN)      | 4032248449019                                                          |
| Qty.            | 250 items                                                              |
| Delivery status | This article will no longer be available in the future.                |
| Available until | 2025-08-31T00:00:00+02:00                                              |

## CLI C 1-6 GE/SW 52 CD

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Dimensions and weights

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Depth      | 5 mm   | Depth (inches)  | 0.1968 inch |
| Height     | 6 mm   | Height (inches) | 0.2362 inch |
| Width      | 4.2 mm | Width (inches)  | 0.1654 inch |
| Net weight | 0.16 g |                 |             |

## Temperatures

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -30...80 °C |
|-----------------------------|-------------|

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## General data

|                                              |                                      |      |
|----------------------------------------------|--------------------------------------|------|
| Material colour according to resistance code | 4                                    |      |
| Orientation of print                         | horizontal                           |      |
| Type of printing                             | Standard                             |      |
| Printing method                              | hot-embossing                        |      |
| Version                                      | CD                                   |      |
| Width                                        | 4.2 mm                               |      |
| UL 94 flammability rating                    | V-0                                  |      |
| Operating temperature range, max.            | 80 °C                                |      |
| Operating temperature range, min.            | -30 °C                               |      |
| Colour                                       | yellow                               |      |
| Halogen                                      | Yes                                  |      |
| Insulation cross-section, max.               | 5                                    |      |
| Basic material                               | PVC, soft, without Cadmium           |      |
| Colour of printing                           | black                                |      |
| Printed characters                           | Numbers                              |      |
| Number of markers per packaging unit         | Form of supply                       | Reel |
| Recommended industries                       | Process, Machinery                   |      |
| Number of markers per combination            | 1 Reel = Conductor and cable markers |      |
| Operating temperature range                  | -30...80 °C                          |      |
| Imprint                                      | 52                                   |      |

## Conductor and cable markers

|                                  |                         |                               |                   |
|----------------------------------|-------------------------|-------------------------------|-------------------|
| Halogen                          | Yes                     | Conductor cross-section, max. | 4 mm <sup>2</sup> |
| Conductor cross-section, min.    | 1.5 mm <sup>2</sup>     | Conductor O.D., max.          | 5 mm              |
| Conductor O.D., min.             | 2.5 mm                  | Conductor O.D.                | 2.5 - 5 mm        |
| Cross-section for connected wire | 1.5 - 4 mm <sup>2</sup> |                               |                   |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ETIM 10.0   | EC001530    | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 |             |             |

**Drawings**



Similar to illustration