

CC 15/27 MC SDR


Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



ClipCard device markers in MultiCard format are used for labelling electrical installations and switchgear systems, and offer an interesting alternative to engraving. Thanks to the proven MultiCard format, labelling is possible with PrintJet CONNECT or Plotter.

- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- Universal fixing
- Carrier (screwable or with cable ties)
- Tag rail (self-adhesive or screw fixing)
- Or self-adhesive tags

For custom printing: Please send us a file of our labelling software M-Print PRO or M-Print PRO Online (without installation) for your labelling specifications.

General ordering data

| | |
|------------|--|
| Version | ClipCard, Device markers, 15 x 27 mm, Holder CC-H 15/27, To customer specification |
| Order No. | 1876630000 |
| Type | CC 15/27 MC SDR |
| GTIN (EAN) | 4032248467143 |
| Qty. | 16 items |

CC 15/27 MC SDR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 1 mm | Depth (inches) | 0.0394 inch |
| Height | 15 mm | Height (inches) | 0.5906 inch |
| Width | 27 mm | Width (inches) | 1.063 inch |
| Net weight | 1.69 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

Environmental Product Compliance

| | | | |
|--------------------------|-----------------------------|------------------|--|
| RoHS Compliance Status | Compliant without exemption | | |
| REACH SVHC | No SVHC above 0.1 wt% | | |
| Product Carbon Footprint | Cradle to gate | 0.014 kg CO2 eq. | |

General data

| | | | |
|--------------------------------------|---|-----------|--|
| Printing method | MC Laser | | |
| Version | pluggable | | |
| Width | 27 mm | | |
| UL 94 flammability rating | V-2 | | |
| Operating temperature range, max. | 100 °C | | |
| Operating temperature range, min. | -40 °C | | |
| Colour | To customer specification | | |
| Halogen | No | | |
| Basic material | Polyamide 66 | | |
| Colour of printing | black | | |
| Printed characters | Requires M-Print PRO File | | |
| Number of markers per packaging unit | Form of supply | MultiCard | |
| compatible printer | PRINTJET CONNECT , MCP BASIC 2 , MCP PLUS 2 | | |
| Number of markers per combination | 1 MultiCard = Device markers | | |
| Operating temperature range | -40...100 °C | | |
| Application/manufacture | Holder CC-H 15/27 | | |

Device markers

| | |
|---------|----|
| Halogen | No |
|---------|----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001288 | ETIM 9.0 | EC001288 |
| ETIM 10.0 | EC001288 | ECLASS 14.0 | 27-28-11-04 |
| ECLASS 15.0 | 27-28-11-04 | | |

CC 15/27 MC SDR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Accessories

www.weidmueller.com

Accessories



General ordering data

| | | |
|------------|----------------------------|---|
| Type | CC-RAIL 1000 | Version |
| Order No. | 1790150000 | ClipCard, Accessories, 1000 x 17 mm, Self-adhesive, black |
| GTIN (EAN) | 4032248213610 | |
| Qty. | 1 ST | |
| Type | CC-RAIL TRANSPARENT1000 | Version |
| Order No. | 1790160000 | ClipCard, Cover, 1000 x 19 mm, Transparent |
| GTIN (EAN) | 4032248213627 | |
| Qty. | 1 ST | |
| Type | CC-H 15/27 | Version |
| Order No. | 1790410000 | ClipCard, Accessories, 15 x 27 mm, black |
| GTIN (EAN) | 4032248215201 | |
| Qty. | 45 ST | |
| Type | STR CC 15/27 TRANSPARENT | Version |
| Order No. | 1888290000 | ClipCard, Accessories, 15 x 27 mm, Transparent |
| GTIN (EAN) | 4032248494163 | |
| Qty. | 80 ST | |
| Type | ETO CC 15/27 TRANSPAR. | Version |
| Order No. | 1880810000 | ClipCard, Accessories, 15 x 27 mm, Transparent |
| GTIN (EAN) | 4032248480890 | |
| Qty. | 10 ST | |