

**WAP WSI4/2****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

**General ordering data**

Version	End plate for terminals, black, Height: 71.12 mm, Width: 2.5 mm, V-0, Wemid, Snap-on: No
Order No.	<a href="#">1880450000</a>
Type	WAP WSI4/2
GTIN (EAN)	4032248541911
Qty.	50 items

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	49.49 mm	Depth (inches)	1.9484 inch
Height	71.12 mm	Height (inches)	2.8 inch
Width	2.5 mm	Width (inches)	0.0984 inch
Net weight	6.52 g		

### Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Product Carbon Footprint	Cradle to gate	0.138 kg CO2eq.	

### Material data

Basic material	Wemid	Colour	black
UL 94 flammability rating	V-0		

### System specifications

Version	End plate
---------	-----------

### Additional technical data

Snap-on	No	Installation advice	Feed-through (bushing)
---------	----	---------------------	------------------------

### Dimensions

TS 32 offset	36 mm	TS 35 offset	36 mm
--------------	-------	--------------	-------

### General

Installation advice	Feed-through (bushing)
---------------------	------------------------

### Classifications

ETIM 6.0	EC000886	ETIM 7.0	EC000886
ETIM 8.0	EC000886	ETIM 9.0	EC000886
ETIM 10.0	EC000886	ECLASS 9.1	27-14-11-33
ECLASS 10.0	27-14-11-33	ECLASS 11.0	27-14-11-33
ECLASS 12.0	27-14-11-33	ECLASS 13.0	27-25-03-01
ECLASS 14.0	27-25-03-01	ECLASS 15.0	27-25-03-01