

**SCREWTY M12 KO O. SD**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



The Screwty® attachment is suitable for M12 round plug-in connectors, with an outside dimension of the knurled nut of  $14.5 \pm 0.3$  mm. The tightening torque is 0.8-1.2 Nm.

**General ordering data**

|            |                                                |
|------------|------------------------------------------------|
| Version    | Cable gland tool adapter for moulded M12 lines |
| Order No.  | <a href="#">1900100000</a>                     |
| Type       | SCREWTY M12 KO O. SD                           |
| GTIN (EAN) | 4032248409952                                  |
| Qty.       | 1 items                                        |
| Packaging  | Plastic bag                                    |

**SCREWTY M12 KO O. SD**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data**

**Dimensions and weights**

|            |        |
|------------|--------|
| Net weight | 14.5 g |
|------------|--------|

**Environmental Product Compliance**

|                        |                       |
|------------------------|-----------------------|
| RoHS Compliance Status | Not affected          |
| REACH SVHC             | No SVHC above 0.1 wt% |

**Screwing tools**

|                   |     |      |         |
|-------------------|-----|------|---------|
| Connection thread | M12 | Size | 14.5 mm |
|-------------------|-----|------|---------|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000149    | ETIM 9.0    | EC000149    |
| ETIM 10.0   | EC000149    | ECLASS 14.0 | 21-01-90-90 |
| ECLASS 15.0 | 21-01-90-90 |             |             |